

| | | | |
|--|--|-------------------|-------------------|
| Department | Standard Components | Room Tag: | 3274 |
| Room Name | Operating Room - CT Control | Room Code: | OR-CTCR-SJ |
| Net Room Area Briefed | 10.0 M2 | | |
| No of Rooms | 1 | | |
| Subtotal of Briefed Area | 10.00 M2 | | |
| Hours of Operation | Available 24 Hours | | |
| Occupancy | Up to 2 staff | | |
| Also covers these Rooms | | | |
| Description/ Special Requirements | <p>Room adjacent to CT Scanning Room/s with direct visibility to the patient for remote control of equipment, and review and reporting of procedure images. The Control room may serve two procedure rooms.</p> <p>Acoustics: Acoustic privacy is required</p> <p>Additional Design Considerations:</p> <ul style="list-style-type: none"> - Radiation shielding as advised by Radiation Consultant - Cable ducts from CT Scanning and Computer room may be required | | |
| Amendment | 14.03.2014 - First Issue | | |

Room Fabric and outline specifications

| ID | Fabric | Material | Finish | Specification | Selection | Remarks |
|------|-----------------|-------------------|-------------------------|------------------------------------|-----------|--|
| 5010 | Ceiling | Plasterboard | Paint, washable | Flush set, suspended | | |
| 6015 | Cornice | Plasterboard | Paint | Flush coved between wall & ceiling | | |
| 8010 | Door protection | Composite | Prefinished PVC | Protection plate to 900AFFL | | |
| 8040 | Door protection | Composite | Prefinished PVC | To door frame | | |
| 9233 | Doors | Solid Core | Prefinished | Single leaf, with lead sheilding | | to Operating Room - CT Procedure |
| 9004 | Doors | Solid Core/ Glass | Paint | Single leaf, observation panel | | corridor side staff entry/ exit; 920mm clear opening; with sliding cover |
| 1000 | Floor finish | Vinyl | Standard slip resistant | Seamless, coved | | |
| 7025 | Observation | Lead glass | Clear | Internal window | | to procedure room |
| 2000 | Skirting | Vinyl | Prefinished | Floor vinyl coved, 150 mmH | | |
| 3000 | Wall finish | Paint | Acrylic, washable | | | |

Fittings and Furniture (FF)

| ID | Description | Category | Group | Qty | Selection / Remarks |
|------|--------------------------|--------------------|-------|-----|---------------------|
| 1050 | Bench: laminate | Furniture/ Fitting | 1 | 1 | |
| 2100 | Chair: ergonomic, office | Furniture/ Fitting | 3 | 2 | |
| 3400 | Coathook | Metalwork | 1 | 2 | |

Department
Room Name

Standard Components
Operating Room - CT Control

Room Tag: 3274
Room Code: OR-CTCR-SJ

| ID | Description | Category | Group | Qty | Selection / Remarks |
|-------|-------------|--------------------|-------|-----|---------------------|
| 24400 | Whiteboard | Furniture/ Fitting | 1 | 1 | 1200 x 900 optional |

Fixtures, Equipment and associated Services (FE)

| ID | Description | Group | Qty | Ele | Data | Cd | W | H | T | W | m | W | Tap | Dns | Gas | Selection / Remarks |
|-------|------------------------------|-------|-----|-----|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----------------------|
| 11400 | Computer: PC & monitor | 3 | 1 | yes | yes | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | |
| 62150 | IMG: console, control | 1 | 1 | yes | yes | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | CT Scanning equipment |
| 54510 | Telephone: handset, standard | 3 | 1 | ___ | yes | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | ___ | |

Services

| ID | Description | Service Category | Qty | Selection / Remarks |
|-------|-----------------------------|------------------|-----|---|
| 1040 | Intercom | Communications | 1 | with handsfree microphone to CT Scan room |
| 1006 | Voice / Data outlet: double | Communications | 4 | 1 outlet for telephone |
| 5000 | Airconditioning | HVAC | | |
| 6000 | General fluorescent | Lighting | | |
| 9001 | GPO: Double | Power | 5 | |
| 9060 | GPO: Special: for equipment | Power | 1 | CT Scanning equipment |
| 12030 | Lead lining | Shielding | | to wall shared with CT Procedure Room |